

Reverse Osmosis Products On Hand

Item No.	Mechanical Schematic Description	Product Description	Product Link
1	Low Pressure Feed Pump	Flotech FP4022 3/4 hp, 230V factory setting, has pressure switch	<a href="#">Flotec FP4022</a>
2	Feed Temp Gauge	Inkbird digital temperature controller. Probe provided was not compatible with set up, incorporated new probe * concerned this controller cannot handle 240v	<a href="#">Inkbird ITC-1000</a>
3	Low Pressure Switch	Gems Sensors 209166 General Purpose Mini Pressure Switch with Zinc-Plated Steel Fitting, 125/250V, 25-75 psi	<a href="#">GEMS Sensor 209166 25-75 PSI</a>
4	High Pressure Pump	F56CH2S4C electric motor 2 hp 56C 1800 rpm 1 phase 115/230 totally enclosed	<a href="#">2 hp motor</a>
5	High Pressure Switch	Gems PS71-30-4MNZ-C-HC Series PS71 General Purpose Mini Pressure Switch, SPDT Circuit, 65-300 psi Range, 1/4" MNPT Steel Fitting, DIN 43650A 9 mm Cable Clamp	<a href="#">GEMS Sensor high pressure</a>
6	Electrical Contactors (4 ea)	Packard C230B 2 Pole 30 Amp Contactor, 120 Voltage Coil, Contactors meet specifications for devices up to 600 VAC	<a href="#">Packard Contactors</a>